



型式	材质	A	A1	A2	A3	B1	B2	B3	C	D	E1	E2	E3	F	G	H
BM10.20.30	PVC	205			178			81	37	183			φ61D×φ110D 软管	259	289	80
	SUS/PVDF	232	176			82			37	183	15A JIS 10K 法兰			258	293	80
	SUS/PTFE	207	126			107			37	183	PT 1/4"			233	293	80
BM50	PVC	230	376	354	214	22	8	63	37	183	15A JIS 10K 法兰	VP16由令	φ91D×φ150D 软管	277	291	80
	SUS/PVDF	233	156			92			38	184	15A JIS 10K 法兰			248	293	80
	SUS/PTFE	209 217	134			103			38 42	184 188	PT 1/4"			237	293	80
BM70-100-120	PVC	238	391	373	323	29	16	54	44	190	15A JIS 10K 法兰	VP16由令	φ91D×φ150D 软管	286	348	104
	SUS/PVDF	239	176			82			43	189	15A JIS 10K 法兰			258	351	104
	SUS/PTFE	217	154			93			43	189	PT 3/8"			247	351	104

BM配件可选择



	配件名称	型号	适用机型
标准配件	虹吸逆止阀	C01	BM10~BM30
		C02	BM50~BM120
可选配件	过滤器	G01	BM10~BM30
		G02	BM50~BM120
	底阀	G03	BM10~BM30
		G04	BM50~BM120

GX系列化学药液过滤机

GX SERIES CHEMICAL LIQUID MEDICINE FILTER

产品特点

- 过滤机桶身及脚座采用模具化生产方式一体成型。
- 过滤机桶身材质可为PP、CPVC、PVDF，依药液酸碱浓度性质及温度特性选择。
- 过滤机焊点业届最少，大幅度降低假性焊接泄漏之虞。
- 选择性采用自吸式或磁驱式泵，其中无轴封磁驱式泵浦能有效防止空转泄漏，污染环境等问题发生。
- 马达防护罩确保马达在酸气中不易受腐蚀。
- 特别适用于电镀液、化学液、纯水循环过滤等用途。
- 可依客户作不同滤材之变化（滤芯式、层叠滤芯式、滤纸式、杨桃式、袋滤式），操作简便。
- 高精度过滤，过滤面积广，效率高，清洗容易。
- 另有钛束环组可供选择。
- 标准配件：出入口由任式或法兰式（含垫片及PVC螺丝）
- 选购配件：开关（含护罩）、底阀或逆止阀、视流器、出入口软管、滤袋等等。

型号识别 Model identification

GX - 1004 - F - U - N - C - J - S - MP
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

①系列代码 Series Symbol	GX
②机型代号 Core-Number	1001-10"×1PCS 2004-20"×4PCS 1002-10"×2PCS 2006-20"×6PCS 2001-20"×1PCS 2008-20"×8PCS 2002-20"×2PCS 2012-20"×12PCS 1004-10"×4PCS 2018-20"×18PCS 3018-30"×18PCS
③滤桶材质 Material of Filter Body	F-PP A-CPVC P-PVDF
④出入口型式 Type of in/outlet	U-由任式 Union F-法兰式 Flange
⑤密封材质 Material of Seal Packing	N-NBR V-VITON

FEATURES

- One piece injected without welding of filter body and stand are adopted the integrative mould and increase the intensity of the filter body with the projection rib .
- According to chemical density and temperature feature to inject the filter body.The material of filter body is made of PP, CPVC, or PVDF.
- The least welding of filter in filter field, it greatly decreases the leakage.
- Assemble with self-priming pump or magnet drive pump is depending on customers. If with magnet drive pump, it can avoid the problems of dry running leakage and environment pollution.
- Motor guard which avoids the motor be corroded in acid environment.
- Excellent application to circulated filtering operations for plating liquid, chemical liquid and pure water.
- According to customer's requirement, various filter elements for choice and easy to operate: Lock Core Filter, Pressure Core Filter, Pressure Layered Core Filter, Bag Filter, Paper Filter, and Bellow Filter.
- The filter provides high precision with wide filter area, high efficiency, easy to operate and clean.
- Titanium (Ti) clamp set also can be provided as choice.
- Standard accessories: union or flange (with gasket and PVC screws)
- Purchase accessories: switch (including guard), foot valve, check valve, flow-seeing tube, in/outlet flexible, or filter bag, etc.

⑥滤材型式 Type of Filter Cores	C-滤芯压板式 Pressure Core Filter B-滤芯螺帽式 Lock Core Filter T-层叠滤芯压板式 Pressure Layered Core Filter K-杨桃滤布式 Bellow Filter P-滤纸式 Paper Filter U-袋滤式 Bag Filter
⑦出入口规格 Specification of In/outlet	J-JIS D-DIN A-ANSI
⑧束环组材质 Material of Clamp	S-SUS304 T-钛 Ti
⑨泵浦型式 Model of Pump	KB Series-自吸式 Self-priming Pump MP Series-磁驱式 Magnetic Drive Pump MPH Series-磁驱式 Magnetic Drive Pump